

RIC speakers pro Marke und Typ

Marke	S-receiver (45 dB)	M-receiver (55 dB)	P-receiver (65 dB)	Filter	Massiv	Folie*	Deep-Fit	Anmerkungen
GN Resound Rie LP/MP/HP, Beltone Rie LP/MP/HP (SF2B)				CeruStop	Option	✓	✓	Surefit 2b.
GN Resound SF2C LP/MP/HP				ProWax	✗	✓	✓	Surefit 2c.
GN Resound Rie LP/MP/HP (SF3)				ProWax	✗	✓	✓	Surefit 3.
GN Resound M + Rie (SF3)				ProWax	✗	✓	✓	Surefit 3.
Signia mini 2.0, Audioservice, Rexton				Quick Guard	Option	✓	✓	Baugleich als RIC2, passt auch in Folien von RIC2.
Signia mini 3.0, Audioservice, Rexton				NanoCare	Option	✓	✓	
Oticon MiniFit, Sonic, Cochlear Nucleus 7				ProWax	✗	✓	✓	
Phonak SDS 4.0, Unitron SDS 4.0				CeruStop	✗	✓	✓	Marvel, Paradise
Phonak SDS 3.0, Unitron 2				CeruStop	Option	✓	✓	Phonak receiver mit Knick (Standard).
Widex Easywear				NanoCare	Option	✓	✓	Befestigungsring in RIC.
Widex V2				NanoCare	Option	✓	✓	
Starkey				CeruStop	✗	✓	✓	
SeboTek				HF3	✓	✗	✗	Im Filter eingeklemmt.

* Bikini RIC ist mit allen Folien möglich.