




RIC overzicht

Merk Type receiver	S-receiver	M-receiver	P-receiver	Aansluiting (bij acrylaat/3D- flex) artikelnummer	Cerumenfilter (in acrylaat (of 3D-flex) maatwerk) artikelnummer
GN Resound SureFit 3 (SF3)	 Low power (LP)	 Medium Power (MP)	 High Power (HP)	 60000249/-250	Prowax (Oticon) 60000251 
GN Resound SureFit 3 (SF3) M&RIE				 60000249/-250	Prowax (Oticon) 60000251 
GN Resound SureFit 2C (SF2C)	 Low Power (LP)	 Medium Power (MP)	 High Power (HP)	 60000249/-250	Prowax (Oticon) 60000251 
GN Resound/Beltone SureFit 2B (SF2B)	 Low Power (LP)	 Medium Power (MP)	 High Power (HP)	 60000065	X (alleen receiver)
Signia/Audioservice/Rexton miniReceiver 3.0	 Standard (S)	 Medium (M)	 Power (P)	 60000123/-121	X (alleen receiver)
Signia Silk X					X (alleen receiver)
Signia/Audioservice/Rexton miniReceiver 2.0	 Standard (S)	 Medium (M)	 Power (P)	 60000270	Quick Guard (Connexx) 60000678 
Oticon/Bernafon/Sonic/ Cochlear (CI) Minifit Receiver	 S - 60dB	 M - 85dB	 P - 100dB	 60000249/-250	Prowax (Oticon) 60000251 
Phonak/Unitron SDS 6.0 / 5.0 / 4.0	 Standard (S)	 Medium (M)	 Power (P)	 60000608/-607	Cerustop (Phonak/Unitron) Waxtron (Oticon) 60000248 
Phonak/Unitron xReceiver (2 pin)	 Standard (xS)		 Power (xP)	 60000243	X (alleen receiver)
Widex Easywear V2		 (Medium (M))	 Power (P)	 60000123/-121	X (alleen receiver)
Widex Easywear	 Standard (S)	 Medium (M)	 Power (P)	 60000123/-121	X (alleen receiver)
Starkey Snapfit 2.0 / Snapfit	 L/40dB	 M/50dB	 P/60dB	 60000608/-607	Cerustop (Phonak/Unitron) Waxtron (Oticon) 60000248 